

# 00595100 & 00596200 CONNECTORS

7-Pole Plastic Body Plug • 24V • ISO 1185 • ISO 3731



00595100  
00595200



00596100  
00596200

## Specifications Overview

<b>Voltage:</b>	24V
<b>Standards:</b>	ISO 1185 ISO 3731

## Web Resources

Download technical resources at:  
[littelfuse.com/connectors](http://littelfuse.com/connectors)

## Description

The plugs consists of a N (Normal) version according to ISO 1185, generally used for standard applications, and a S (Supplementary) version according to ISO 3731 used for additional connections. The latter can be distinguished by its white coloring and by the different order of the contacts , preventing thus an incorrect connection to the N version.

## Features and Benefits

- Standards: Conforms to ISO 1185 & ISO 3731 recommendations and standards.
- Accepts all 7-pole sockets that conform to ISO 1185 & ISO 3731.
- The screw contacts version is mainly intended for the replacement market (aftermarket)
- The flat terminals version is generally preferred by harness manufacturers.

## Accessories

PART NUMBER	IMG.	SOCKET	DESCRIPTION OF ACCESSORIES
00600800 (10 pcs)	1	00595100 00596100 00595200 00596200	Rear protecting cap for plug 24V 7 pole
00601000 (5 pcs)	2	00595100 00596100 00595200 00596200	Antikink spring + protecting cap for 7 pole 24V plug
00600100 (1 pcs)	3	00595200 00596200	Wired flat terminal coupling for 7 pole 24V plug
00603100 (1 pcs)	4	00595200 00596200	Flat terminal coupling for 7 pole 24V plug
00603160 (100 pcs)	4	00595200 00596200	Flat terminal coupling for 7 pole 24V plug

## Ordering Information

PART NUMBER			ISO	PIN MATERIAL NUMBER	TERMINAL TYPE
BOXED 1 pcs.	BULK 100 pcs.	BULK 100 pcs. <input checked="" type="checkbox"/>			
00595100	00595190	00595199	1185	7 pole Nickel-plated brass	screw
00595200	00595290	00595299	1185	7 pole Nickel-plated brass	flat
00596100	00596190	00596199	3731	7 pole with 16 rear contacts Nickel-plated brass	screw
00596200	00596290	00596299	3731	7 pole Nickel-plated brass	flat

