
















HVAC Selection Guide

Protect and Control the Critical Components in your HVAC Systems

	LITTELFUSE PRODUCT & PART NUMBER	BENEFITS	FEATURES	COMPETITOR PART NUMBERS
VOLTAGE MONITORS	Three-Phase Voltage Monitors 460 	Protects compressors and blower motors from adverse voltage conditions that can cause damage to the motor windings.	<ul style="list-style-type: none"> ■ Universal range from 190 to 480 V ac or 475 to 600 V ac and 50/60 Hz ■ Transient protection meets IEEE and IEC standards ■ Four adjustment pots provide versatility for a variety of applications ■ Adjustable trip delay and restart delay ■ Standard surface or DIN-rail mountable 	Diversified: SLU100ASD Time Mark: Series 158 ICM Controls: ICM 401 for up to 480 V ac Macromatic: PMDU Agastat: PMA series Crouzet: UFR2 series Electronics: PVC400AR
	Three-Phase Voltage Monitors 250A 	Protects compressors and blower motors from adverse voltage conditions that can cause damage to the motor windings.	<ul style="list-style-type: none"> ■ Protection from low and high voltage, unbalance, single-phase, and reverse-phase conditions ■ LED diagnostics is quick visual indicator for cause of trip ■ Adjustable trip delay to prevent nuisance tripping ■ DPDT relay output 	A-1 Components: EAC-800 series Diversified: SLA*, SLC*, SLM* R-K Electronics: PVCL Time Mark: Series 2642, 2644 Watsco: EAC-800 *If 2 Form C contacts are required, SLJ-XXX-ALE
	Three-Phase Voltage Monitors 455 	Provides all the same voltage/phase protection as the 460 model, but with three added advantages listed in the features section.	<ul style="list-style-type: none"> ■ Second set of voltage inputs for monitoring voltage on the load-side of the motor contactor to detect contact failure ■ Keeps history of the past 20 fault causes ■ Wirelessly download and view fault history 	ICM Controls: ICM450, ICM400 A-1 Components: EAC-8001 Watsco: EAC-8001
	Three-Phase Voltage Monitors 201A 	Protects compressors and blower motors from adverse voltage conditions that can cause damage to the motor windings regardless of size.	<ul style="list-style-type: none"> ■ Protection for low voltage, voltage unbalance, phase reversal, and harmful power line conditions. ■ Optional high-voltage monitoring 	Time Mark: 253, 257B Macromatic: PMPU-FA8
Other available voltage monitors commonly used for HVAC applications are 201A-9, 460, 460-575, 460-14, 250A, 202, 455, and 460-200-SP				
LOAD/CURRENT SENSORS	Self-Powered GO/NO GO Ac Current Sensors LSRX-C, LSRX 	The LSRX/LSRX-C series is designed to energize the output contact whenever 4.5 Amps or greater is present. Used commonly as an ac current proof relay to indicate if a motor is operating.	<ul style="list-style-type: none"> ■ Self-powered ■ Quick-connect terminals reduce installation time ■ Built-in current sensor eliminates the need for a stand alone current transformer 	Diversified: CMG-0100-20, CMG-0100-24, CMG-0100-28, CMG-0100-32, CMG-0100-36, CMG-0200-20, CMG-0200-24, CMG-0200-28, CMG-0200-32, CMG-0200-36
	Other available load/current sensors commonly used in for HVAC applications are LSR-24, LSR-115, ECS30AC, ECS31AC, ECS40AC, ECS41AC, ECS4HBC			
AC CURRENT TRANSDUCERS	Ac Current Transducers TCSA20 	Varies the effective resistance of its output in direct proportion to the current flowing in the conductor it is monitoring.	<ul style="list-style-type: none"> ■ Monitors 0 to 20 A ■ Loop powered from 10 to 30 V dc ■ Linear output from 4 to 20 mA 	AcuAMP ACT050-42L-S (split core 0 to 50 A) Hawkeye H721HC (0 to 30 A)
	Other available ac current transducers commonly used for HVAC applications are TCSA5, TCSA10, TCSA50			
TYPE 2 SURGE PROTECTION DEVICES	Type 2 Surge Protection Devices SPD2 	Positioned at the power distribution or branch circuit location, it safeguards components from power fluctuations or surges by limiting the fault current to a load or the unit being protected to prevent equipment damage or downtime.	<ul style="list-style-type: none"> ■ Capability to clamp and withstand high-energy transients to prevent disruption, downtime, and degradation or damage to equipment ■ Thermal protection to eliminate catastrophic failure ■ UL Recognized and IEC Compliant in one part number to reduce inventory and support global usage ■ DIN-rail mounted and compact footprint to increase panel design flexibility ■ An SPD type and voltage-coded plug to prevent module from being placed in wrong base, eliminating the risk of improper protection 	ABB: OVR T2 80-...s P TS QS, OVR T2 40-...s P TS QS Bourns: 1250, 1420 Citel: DS40, DS40VG, DS70R DEHN: DEHNguard M, DEHNguard S Phoenix Contact: VALVETRAB-SEC-T2 Raycap: ProTec T2

HVAC Selection Guide

Protect and Control the Critical Components in your HVAC Systems

	LITTELFUSE PRODUCT & PART NUMBER	BENEFITS	FEATURES	COMPETITOR PART NUMBERS
TIME DELAY RELAYS	Delay-on-Make Timers ¹ TMV8000 	Used to delay the blower from turning on, in a heating/cooling system, to allow time for the system to reach temperature before forcing air through the ventilation ducts. Also used to stagger start for multiple compressors within a facility, on start up or after a power outage.	<ul style="list-style-type: none"> Universal ac/dc operating voltage Two terminal series connection with the load Solid state prevents arc and wear over time Encapsulated to protect against shock vibration 	Macromatic: THL-1024U-32 Ametek NCC: Q1T-00600-311 Diversified and Time Mark: Several (Contact technical support)
	Delay-on-Break Timers ² TDUB3000A 	Used to delay the blower from turning off, in a heating/cooling system, after the demand has been met to allow all of the conditioned air to be forced out of the ventilation ducts.	<ul style="list-style-type: none"> 24 to 120 V ac input voltage User selectable time delay Solid state prevents arc and wear over time Encapsulated to protect against shock vibration 	Macromatic: THR-11662-31T, POM Airotronics: TGML10100A1
	HVAC-R Timers CT1S45 	The CT series timers combine a delay-on-make and delay-on-break time delay into one unit and may be used to control fan delays in heating and/or cooling equipment.	<ul style="list-style-type: none"> Delay-on-make and delay-on-break in one unit Voltage 24 V ac input voltage Solid state prevents arc and wear over time Encapsulated to protect against shock vibration 	The CT series timers can replace several competitors' delay-on-make and delay-on-break dual-function HVAC timers. (Contact technical support)
	Multifunction Timers TRU1, TRU2 & TRU3 	A multifunction universal time-delay relay. Six timing functions include delay-on-make, interval, single shot, recycling (ON time first, equal recycle delays), delay-on-break, and retriggerable single shot.	<ul style="list-style-type: none"> Universal input voltage Knob adjustable time delay LED indicators provide visual indication of input voltage and relay status 	TRU2: Diversified: All series of TBD, TBE, TUD-120-AKA, TUE-120-AFA, TUE-120-A Macromatic: TD-7, TD-8 TRU3: Diversified: TBD-XXX-XXX-D, TBE-XXX-XXX-D, TDD-XXXAKA-XXX, TDE-XXX-AKA-XXX, TDU, 314 IDEC: RTE-PFX, RTE-PSX, RTEL-PFX, RTEL-PSX Macromatic: TD-7, TD-8 ICM Controls: ICM500 Series
UL CLASS FUSES, HOLDERS & DISTRIBUTION BLOCKS	Class CC & Midget Fuses CCMR, KLDR, KLKR, KLKD 	Littelfuse UL fuses protect your system from overload and short circuit. Littelfuse fuses are chosen over breakers due to their higher amperages, quicker response time, easy coordination, and no calibration required.	<ul style="list-style-type: none"> Compact design is ideal for space saving protection High-interrupting capacity and excellent current-limitation 	Busmann: LPCC, FNQR, KTKR Mersen: ATDR, ATQR, ATMR, ATM
	Class R fuses FLNR, FLSR 		<ul style="list-style-type: none"> High short-circuit current rating Dual-element design Available with and without indication 	Busmann: FRNR, FRSR Mersen: TR, TRS
	Class T Fuses JLLN, JLLS 		<ul style="list-style-type: none"> Extremely current-limiting 200 kA interrupting rating 	Busmann: JJN, JJS Mersen: A3T, A6T
	Class J Fuses JTD 		<ul style="list-style-type: none"> Superior time-delay and cycling characteristics Available with and without indication 	Busmann: LPJ Mersen: AJT
Littelfuse offers a wide variety of UL approved open face, finger safe, and panel mount fuse holders including: LFT series (Class T), LFR series (Class R), LFJ series (Class J), as well as L600 30C, LPSC, and 571/572 series for Class CC. Visit our website for a full list of blocks and holders.		Littelfuse also offers a wide array of power distribution blocks. Visit the Littelfuse website to see our full offering.		Littelfuse has alternatives to standard fuse holders and distribution blocks from Busmann, Mersen, and Marathon.

¹ Delay-on-Make Timer: Upon application of input voltage, the time delay (t) begins. The output is de-energized before and during the time delay, but then becomes energized at the end of the time delay (t).

² Delay-on-Break Timer: Once input voltage is applied, the time delay relay is ready to be activated. When the relay is activated, the output is energized. Then when the the relay is deactivated, the time delay begins and the output remains energized during timing. At the end of the time delay, the output becomes de-energized.

This tool is intended to be used as a guide only. Check our cross reference document for a full list of competitor products substitutable with Littelfuse Class CC, RK5 & Class T Fuses. The user will need to verify the part is appropriate for the application. Contact our technical support team at 1-800-TEC-FUSE (1-800-832-3873) or techline@littelfuse.com.